

ECO NO.	REV.
ECO 07824	A
ECO-08281	B




TABLE 1

ELMO P/N	LENGHT IN METERS	LABEL
CBL-PML80WOBR48V	2.0 m	CBL-PML80WOBR48V
CBL-PML80WOBR48-5	5.0 m	CBL-PML80WOBR48-5

COLOR	FROM J1	TO	SIGNAL
WHITE	1	ENDING FERRULE	M1
RED	2	ENDING FERRULE	M2
BLACK	4	ENDING FERRULE	M3
	5	NC	
	6	NC	
GREEN	⏏	ENDING FERRULE	PE

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
1	WIP-024X14	14 AWG SINGLE CROSS OVER	1
2	STB-29520	BLACK SRINK 3/8 "	20mm
3	JCF-031514G8	ENDING FERRULE 14 #	4
4	JCW-M23P06A	M23 POWER CIRCULAR PLUG 6PINS INTERCONTEC P/N: BSTA107NN00080236000	1
5	JCW-M23PCF2	M23 POWER CRIMP TERMINAL SPRING D=2MM FEMALE INTERCONTEC P/N: 60.254.11	4
6	LABEL	SEE TABLE 1.	1
7	STB-21170	BLACK SRINK 3/64 "	4 X 10 mm

ALL DIMENSIONS ARE IN MM.

DO NOT MEASURE THE DRAWING.  
ALL DIMENSIONS BEFORE COATING.

FILE NAME: MD-00632B.sldprt

NOTES: COVER EACH WIRE IN J1 WITH ITEM 7

RoHS Compliance

	NAME	SIG	DATE
DRAWN	A.C.		21/08/2014
DESIGN	RamiCh		21/08/2014
CHECK			
APVD.	-		-



TITLE			
Motor Cable, M23, 25A			
SIZE	SCALE	DWG. NO.	REV.
A3	1:2	MD-00632	B
PAGE: 1 OF: 1		CAT. NO. CBL-PML80WOBR48V	