

INDEX

Type	Section	Report Date	Approvals
Power Conversion Equipment, DC Motor Controller, Model DAC-8.	1	1996-05-20	
Power Conversion Equipment, Models PIC followed by 5/55, 15/55, 3/100, 10/100, 2/200, 6/200, 15/100, 15/200 or 25/50; FLU followed by 5/55, 15/55, 5/60, 10/60, 15/60, 25/60, 3/100, 10/100, 2/200, 6/200, 15/100, 15/200 or 25/50; VIO followed by 15/55, 5/60, 10/60, 15/60, 25/60, 10/100, 6/200, 15/100, 15/200 or 25/50 - may be followed by K	2	1998-07-08	
Power Conversion Equipment, SAX Drive Series, Model SAX 3/230, 5/230, 3/400, 4/400, 8/400, 10/400, 14/400, may be prefixed by P, PP or M, may be suffixed by "X".	3	2000-10-30	
Withdrawn	4	2000-10-31	
Power Conversion Equipment, Model CLA followed by 5/55, 15/55, 3/100, 10/100, 2/200, 6/200, 15/100, 15/200 or 25/50 - may be prefixed by P, PP, may be suffixed by "X".	5	2001-12-28	
Power Conversion Equipment, Drive Series. Models Harmonica and Banjo 5/60, 8/60, 12/60, 2/100, 4/100, 8/100, 12/100, 04/200, 1/200, 2/200, 4/200, 6/200. Cello 5/60, 10/60, 15/60, 30/60, 15RMS/60, 3/100, 10/100, 15/100, 15RMS/100, 30/100, 2/200, 6/200, 10/200, 15/200, 15RMS/200. Bassoon 1/230, 3/230, 5/230, 6/230. Trumpet 5/60, 10/60, 15/60, 15RMS/60, 3/100, 10/100, 15/100, 15RMS/100, 2/200, 6/200, 10/200, 15/200, 15RMS/200.	6	2005-04-21	

Type	Section	Report Date	Approvals
Power Conversion Equipment, Drive Series. Cornet series, Models COR may be followed by A, followed by 1/230, 3/230, 5/230, 7/230, 9/230, 1/460, 3/460 or 6/460 may be followed by a letter. See nomenclature breakdown for further information.	7	2007-10-12	
Tuba series, Models TUB may be followed by A, followed by 12/230, 15/230, 20/230, 12/460, 15/460 or 20/460, may be followed by a letter	8	2008-04-24	B
Series Whistle, Models WHI, may be followed by A, followed by 10/48, 15/48, 20/48, 1/60, 2.5/60, 5/60, 10/60, 15/60, 20/60, 1/100, 2.5/100, 5/100, 10/100, 15/100 or 20/100 may be followed by a letter, with or without suffix SOL. Series Hornet, Models HOR-10/48, HOR-15/48, HOR-20/48, HOR-1/60, HOR-2.5/60, HOR-5/60, HOR-10/60, HOR-15/60, HOR-20/60, HOR-1/100, HOR-2.5/100, HOR-5/100, HOR-10/100, HOR-15/100, HOR-20/100, with or without suffix SOL. Series Ocarina, Models OCA, may be followed by A, 10/48, 15/48, 20/48, 1/60, 2.5/60, 5/60, 10/60, 15/60, 20/60, 1/100, 2.5/100, 5/100, 10/100, 15/100, 20/100 may be followed by a letter.	9	2008-05-07	B

(Table Cont'd)

Models	Section	Report Date	Approvals
Guitar Series: GUI-20/48, GUI-25/48, GUI-35/48, GUI-20/60, GUI-25/60, GUI-35/60, GUI-20/100, GUI-25/100, GUI-50/100 , GUI-3/200, GUI-6/200, GUI-10/200, GUI-17/200, GUI-R45/48, GUI-R45/60, GUI-R35/100, GUI-R30/200, with or without prefix SOL. Hawk Series: HAK-20/48, HAK-25/48, HAK-35/48, HAK-20/60, HAK-25/60, HAK-35/60, HAK-20/100, HAK-25/100, HAK-50/100 , HAK-3/200, HAK-6/200, HAK-10/200, HAK-17/200, HAK-R45/48, HAK-R45/60, HAK-R35/100, HAK-R30/200, with or without prefix SOL. Drum Series: DRU-70/48, DRU-R90/48, DRU-70/60, DRU-R90/60, DRU-50/100, DRU-R75/100, DRU-35/200, DRU-R60/200, DRU-18/400.	10	2009-06-19	B

Table Continued

Models	Section	Report Date	Approvals
<p>Eagle Series: EAG-70/48, EAG-R90/48, EAG-70/60, EAG-R90/60, EAG-50/100, EAG-R75/100, EAG-35/200, EAG-R60/200, EAG-18/400.</p> <p>Cymbal Series: CYM-70/48, CYM-R90/48, CYM-70/60, CYM-R90/60, CYM-50/100, CYM-R75/100, CYM-35/200, CYM-R60/200, CYM-18/400.</p> <p>Condor Series: CON-70/48, CON-R90/48, CON-70/60, CON-R90/60, CON-50/100, CON-R75/100, CON-35/200, CON-R60/200, CON-18/400.</p>	10	2009-06-19	B
<p>Trombone Series: TRO-1/400, TRO-6/400, TRO-6.1/400, TRO-12/400, TRO-16/400, TRO-R17/400, TRO-R22/400, TRO-8/800, TRO-12/800, TRO-R11/800, TRO-R16/800, with or without prefix SOL- or DC-.</p> <p>Panther Series: PAN-1/400, PAN-6/400, PAN-6.1/400, PAN-12/400, PAN-16/400, PAN-R17/400, PAN-R22/400, PAN-8/800, PAN-12/800, PAN-R11/800, PAN-R16/800, with or without prefix SOL- or DC-.</p> <p>GOLD-Trombone Series: G-TRO1/400, G-TRO6/400, G-TRO6.1/400, G-TRO12/400, G-TRO16/400, G-TROR17/400, G-TROR22/400, G-TRO8/800, G-TRO12/800, G-TROR11/800, G-TROR16/800, with or without prefix SOL- or DC-.</p> <p>GOLD-Panther Series: G-PAN1/400, G-PAN6/400, G-PAN6.1/400, G-PAN12/400, G-PAN16/400, G-PANR17/400, G-PANR22/400, G-PAN8/800, G-PAN12/800, G-PANR11/800, G-PANR16/800, with or without prefix SOL- or DC-.</p> <p>Tambourine Series: TAM-20/36, TAM-20/60, TAM-20/120, TAM-20/230, TAM-20/480</p>	11	2012-06-27	B

*

G-BAS, may be followed by R, followed by 1, 3, 6, or 10, followed by 120 or 230.	12	2014-05-30	B
G-TUB, may be followed by R, followed by 20, 25, 30, 40, or 45, followed by 230 or 480.	13	2014-05-31	B
G-DRU or G-EAG, may be followed by R, followed by 35, 50, 70, or 100, followed by 400 or 800.	14	2014-06-01	B
TAM-100, followed by 120, 230, 420, 460, or 480.	15	2014-06-02	B
G-WHI, G-DCWHI, G-SOLWHI, or G-SOLHOR, may be followed by R, followed by 1/100, 2.5/100, 3/100, 5/100, 10/100, 15/100, 20/100, 3/200, 6/200, 9/200, or 10/200, may be followed by E, S, T, or G. DC-WHI, may be followed by A, followed by 1/100, 2.5/100, 3/100, 5/100, 10/100, 15/100, or 20/100. SOL-HOR, may be followed by 15/48, 20/48, 1/60, 2.5/60, 5/60, 10/60, 15/60, 20/60, 1/100, 2.5/100, 3/100, 5/100, 10/100, 15/100, 20/100, 3/200, 6/200, 9/200 or 10/200. G-DUO, may be followed by R, followed by 0101/100, 0202/100, 0303/100, 0505/100, 1010/100, 1515/100, 2020/100, 0303/200, 0606/200, 0909/200, or 1010/200, followed by E or S.	16	2015-03-20	B
G-BEL, may be followed by R, followed by 1/100, 2.5/100, 3/100, 5/100, 10/100, 15/100, 20/100, 3/200, 6/200, 9/200, or 10/200, followed by E or S. G-DCBEL or G-CLA, may be followed by R, followed by 1/100, 2.5/100, 3/100, 5/100, 10/100, 15/100, 3/200, 6/200, 9/200, or 10/200, may followed by E, S, or F.	17	2015-03-21	B
G-GUT, G-SOLGUT, G-HAK, G-SOLHAK and G-CEL may be followed by R, followed by 20/48, 25/48, 35/48, 45/48, 75/48, 20/60, 25/60, 35/60, 45/60, 50/60, 75/60, 20/100, 25/100, 35/100, 50/100, 3/200, 6/200, 10/200, 17/200, 20/200, 25/200 or 30/200, may be followed by E, S, T, or G.	18	2015-10-13	B
G-DRU, G-EAG may be followed by R, followed by 70/48, 90/48, 70/60, 90/60, 50/100, 60/100, 75/100, 100/100, 150/100, 35/200, 60/200 18/400, 20/400, or 26/400, may be followed by E, S, T, or F.	19	2015-10-16	B
G-OBO, may be followed by R, followed by 1/230, 3/230, 6/230, 10/230, 13/230, 1/480, 3/480, 6/480 or 10/480, may be followed by S,F,E, may be followed by E, R, may be followed by suffix.	20	2016-03-01	B

Models	Section	Report Date	Approvals
<p>G-TWI, G-BEE, G-SOLTWI, or G-SOLBEE, may be followed by R or P, followed by 2/48, 25/50, 5/55, 10/55, 15/55, 1/60, 2/60, 3/60, 4/60, 5/60, 6/60, 10/60, 12/60, 15/60, 20/60, 25/60, 30/60, 50/60, 30/80, 40/80, 80/80, 100/80, 1/100, 2/100, 3/100, 4/100, 5/100, 6/100, 10/100, 12/100, 15/100, 20/100, 25/100, 30/100, 35/100, 45/100, 50/100, 70/100, 45/150, 1/200, 2/200, 3/200, 4/200, 5/200, 6/200, 10/200, 12/200 or 15/200, 20/200, 25/200, 30/200, or 35/200, may be followed by S, E, or M, may be followed by E or R, may be followed by 1 through 9, may be followed by S or H, may be followed by additional suffixes.</p> <p>VIO, CAN, PIC, ROB, FLU, or RAV, may be followed by R, followed by 2/48, 25/50, 5/55, 10/55, 15/55, 1/60, 2/60, 3/60, 4/60, 5/60, 6/60, 10/60, 12/60, 15/60, 20/60, 25/60, 30/80, 40/80, 1/100, 2/100, 3/100, 4/100, 5/100, 6/100, 10/100, 12/100, 15/100, 20/100, 25/100, 30/100, 35/100, 45/100, 1/200, 2/200, 3/200, 4/200, 5/200, 6/200, 10/200, 12/200, 15/200, 20/200, 25/200, 30/200, or 35/200, may be followed by suffix, followed by G.</p>	21	2016-03-24	B
<p>GOLD-DOUBLE TWITTER/DOUBLE BEE Series:</p> <p>G-TWID, G-BEED, G-SOLTWID, or G-SOLBEED, followed by 180/60, 160/80, 140/100, 100/150, 40/200 or 70/200, may be followed by S or E, may be followed by E or R, may be followed by S, T, X, Y, Z, D, or H, may be followed by D or V, may be followed by suffix.</p> <p>GOLD-TRIPLE TWITTER/TRIPLE BEE Series:</p> <p>G-SOLTWIT, or G-SOLBEET, followed by 270/60, 240/80, 210/100, 150/150 or 100/200, may be followed by S or E, may be followed by E or R, may be followed by S, T, H, X, Y, or Z, may be followed by D or V, may be followed by suffix.</p>	22	2021-07-23	B
<p>GOLD-MANDOLIN/JAGUAR Series:</p> <p>G-MAN, G-JAG, G-SOLMAN, or G-SOLJAG, followed by 1/400, 3/400, 5/400 or 7/400, may be followed by S, E, may be followed by E, R, may be followed by S, T, H may be followed by suffix.</p>	23	2021-08-20	B

Models	Section	Report Date	Approvals
PCIM, followed by -B or -L, followed by F or O, followed by -R, followed by 8, 16, 25, or 50, followed by /800, followed by E or S, followed by E, R, H, 1, 2, 3 or 4 followed by K, L or N, may be followed by multiple alphanumeric characters.	24	2021-10-21	B
PTWT or PBET, followed by -S, followed by F, S, T, O, or N, followed by -R, followed by 270/60, 240/80, 210/100, 100/200, followed by E or G, followed by E, R, H, 1, 2, 3, or 4, followed by U, V, or B, may be followed by Q, may be followed by additional suffixes	25	2021-12-30	B
PTWI or PBEE, followed by -W, -V, -H, or -M, followed by F, S, T, O, or N, followed by -1/100, -3/100, -6/100, -10/100, -15/100, -25/100, -3/200, -6/200, -10/200, -R80/80, -R50/100, -R70/100, R45/150, R15/200, or R35/200, followed by E, G, or S, followed by E or R, may be followed by U, V, or B, may be followed by -H, may be followed by Q, may be followed by additional suffixes.	26	2021-12-31	B
PSTR, followed by -B or -L, followed by O, may be followed by -R or -C01 up to C99, may be followed by 3, 4, 5, 6, 8, 10, 15 or 16, followed by /400, followed by F or S, followed by E, followed by U, or V, may be followed by Q, may be followed by additional suffixes.	27	2023-05-25	B
PBAS, followed by -B or -L, followed by F, S, or O, may be followed by -R, followed by 1, 3, 5, 6, 9, or 10, followed by /230, followed by F or S, followed by E, R, H, 1, 2, 3, or 4, followed by U, V, or W, may be followed by Q, may be followed by additional suffixes	28	2023-11-09	B

Approval Abbreviation:

A - Evaluated to United States Standards Only

B - Evaluated to United States Standards and Canadian National Standards

C - Evaluated to Canadian National Standards Only